



*Trinocular LED fluorescence microscope,
1000x, IOS W-PLAN objectives*

Observation Method - Transmitted Light	Brightfield	Yes
	Phase contrast (Positive type)	As optional
	Darkfield	As optional
	Simple polarized light	As optional
Observation Method - Incident Light	Fluorescence	Yes
Main Body	Type	Upright
	Construction material	Aluminum die-cast
	Transportation handle	Yes
Head	Type	Trinocular (Siedentopf)
	Split ratio	100/0 - 50/50 - 0/100
	Inclination	30°
	360° rotating	Yes
	Interpupillary distance (mm)	50-75
	Dioptric adjustment	On left tube
	Tube inner diameter (mm)	30
Eyepieces	Field number (mm)	22
	Magnification	10x
	Planar type	Yes
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	26
	High eyepoint (for glass wearers)	Yes
	Rubber cup	Yes
	Retractable protections	Yes
Nosepiece	Positions	Quintuple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
Objectives	Optical system	∞
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	40x-1000x
	Type	IOS W-PLAN
		4x/0.10, W.D. 17.3 mm
		10x/0.25, W.D. 10 mm
		40x/0.65, W.D. 0.54 mm 100x/1.25 (Oil), W.D. 0.13 mm

Stage	Type	Double layer
	Dimensions (mm)	233x147
	Moving mechanism	Rackless
	Moving range (mm)	78x54
	Material	Anti-scratch painting
	Specimen holder	Yes
	Slide number	2
	X-Y Vernier scale	Yes
	Vernier scale accuracy (mm)	0.1
Condenser - Single Position	Type	Swing-out
	Removable	Yes
	Numerical aperture (N.A.)	0.2 / 0.9
	Numerical aperture scale	Yes
	Diaphragms	Iris
	Centrable	Yes
	Focusable	By rack and pinion
Focusing System	Type	Coaxial coarse & fine
	Coarse total travel (mm)	25
	Fine total travel (per single rotation) (mm)	0.2
	Fine graduations	100
	Fine resolution (µm)	2
	Upper stop to prevent contact	Yes
	Adjustable tension	Yes
	Flat knob for ergonomoy	Yes
Transmitted Illumination	Kohler illumination	Full
	Type	X-LED
	X-LED type	X-LED3
	Light source power (W)	3.6
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	6
Power Supply for Transmitted Illumination	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	6 Vdc 2.5 A
Accessories Included	Dust cover	Yes
	Immersion oil (10ml)	Yes
	Tension adjustment tool	Yes
	Allen wrench	Yes
	User Manual	Digital version (downloadable)
Additional Information		Heating stage (as optional). External rechargeable battery pack (as optional).
Product Dimensions	Height (mm)	490
	Width (mm)	276
	Depth (mm)	395
Product Weight	(kg)	11.5

Fluorescence Attachment	Number of positions	4
	Filter dimensions	Excitation: 25 mm diam.; Dichroic: 36 mm x 25 mm; Emission: 25 mm diam.
	Filter set selection	Manual
	LED source insertion	Manual

Fluorescence Light Source	Light source	<i>See optional LED Fluorescence Cube list</i>
	Brightness control	Yes

Fluorescence Power Supply	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	12 Vdc 1.5 A